

<b>Bemerkung:</b> manuelle Eingabe			
Material Bez:	Metallpulver		
Datum:	18. Februar 2016	<b>Gusskugel</b>	<b>Alupulver</b>
Charge:	-	<b>Messung 1</b>	<b>Messung 2</b>
Prüfer:	Jess	<b>432532</b>	<b>432532</b>
Messgerät:	RA-MA60		
Ser-Nr.:	<b>432532</b>		
Druckzeit in sek ->	<b>10</b>	25,5698	28,1548
	0,2	0,0073	0,0028
	0,3	0,0278	0,0070
	0,5	0,1674	0,0125
	0,7	0,3249	0,0218
	0,8	0,5422	0,0363
	1,0	0,7976	0,0581
	1,2	1,0747	0,0895
	1,3	1,3219	0,1318
	1,5	1,5325	0,1819
	1,7	1,6850	0,2400
	1,8	1,7944	0,3035
	2,0	1,8718	0,3743
	2,2	1,9168	0,4494
	2,3	1,9359	0,5309
	2,5	1,9376	0,6163
	2,7	1,9391	0,8009
	2,8	1,9404	0,9069
	3,0	1,9415	0,9484
	3,2	1,9424	0,9987
	3,3	1,9428	1,0840
	3,5		1,1692
	3,7		1,2457
	3,8		1,3081
	4,0		1,3561
	4,2		1,3916
	4,3		1,4178
	4,5		1,4390
	4,7		1,4560
	4,8		1,4696
	5,0		1,4770
	5,2		1,4794
	5,3		1,4801
	5,5		1,4804
	5,7		1,4804
	5,8		1,4806
	6,0		1,4807
	6,2		
	6,3		
	6,5		
	6,7		
	6,8		
	7,0		

Ser-Nr. Waage  
soll Temp.  
Definieren  
Startgewicht / g

**Mat-Bez:** Metallpulver  
**Charge:** -  
**Datum:** 18. Februar 2016  
**Typ: RA-MA 60** 432532

